

# HICAPSEAL125


## Capsule Sealing Machine

### Features and Benefits

- Check function whether or not capsules are sealed (at customer's option, only if there is color difference)
- Automatic regular rehydration function to seal liquid (at customer's option)
- The seal roller height and sealing position are independent adjustment mechanism. They can be adjusted even during machine operation
- The seal slat and the drying carrier are can be attached and detached in a single operation.
- Parts in direct contact with pharmaceuticals can be attached and detached without tools.
- Drying unit is separable to easily upgrade drying capacity.
- Compact size, the footprint is the smallest in its class.



**Made in Japan**



Model	HICAPSEAL 125
Processing speed	Max 125,000 (caps/h)
Hard Capsule Size	000, 00, 0, 1, 2, 3, 4, 5
Dimensions (W)X(D)X(H)	2,150mm×690mm×2,050mm

Weight	Main body 700kg, Drying Unit 500kg
Power Source	3 phase 200V 50/60Hz 2.0KVA
Compressed Air	0.5MPa 350L/min
Vacuum	8kPa 3 m <sup>3</sup> /min